

► Manual Stages ► High-Grade Stages

Motorized
Stages

Automated
Products for
Microscopes

Fix Stages

Thin VBV
Stages

Rack & Pinion
Stages

High-Grade
Cross Roller
Stages

Sim Stages,
Z Lift Stages,
Z Stages

Rotary Stages

Tilt/Tilt
Stages

Tilt/Rotary
Stages

XZ, YZ Stages

X/Z Stages

High-Grade XY Stages 40 x 40 (Stainless Steel)

 HG-VCR
method




↑ TLD-4042-C1



↑ TLD-4042-C6



↑ TLD-4042-C8



↑ TLD-4042-S1



↑ TLD-4042-S6



↑ TLD-4042-S8


Features

- A high-accuracy, high-rigidity stage using the HG-VCR method.
- Standard types and symmetrical types are available for a left-right symmetrical structure.
- Feed screws, standard micrometers, and fine pitch micrometers are available for the feed method.
- Clamp method is with a plate clamp.
- Versatile use for precision positioning of cameras, sensors, workpieces, and more.

Model number (standard)	TLD-4042-C1	TLD-4042-S1	TLD-4042-C6	TLD-4042-S6	TLD-4042-C8	TLD-4042-S8				
Model number (symmetrical)	TLD-4042-CR1	TLD-4042-SR1	TLD-4042-CR6	TLD-4042-SR6	TLD-4042-CR8	TLD-4042-SR8				
Model name	High-Grade XY Stage 40 x 40									
Travel direction	XY-axis double direction									
Stage surface	40 mm x 40 mm									
Clamp method	Plate clamp									
Operating part mounting position	Center	Side	Center	Side	Center	Side				
Feed method	CMH-13RM (standard micrometer)		Feed screw P=0.5 mm		MHS4-6.5FP (Fine pitch micro)					
Travel amount	± 6.5 mm			± 3 mm						
Travel amount/1 knob rotation	0.5 mm			0.1 mm						
Scale	Micrometer 0.01 mm		-		Micrometer 0.002 mm					
Sensitivity	0.003 mm		0.01 mm		0.001 mm					
Travel guide	HG-VCR (V-groove and cross rollers)									
Travel accuracy	Straightness (horizontal/vertical): 0.001 mm Yaw 15 s, pitch 25 s									
Permissible moment	Yaw 500 N·cm, pitch 500 N·cm, roll 500 N·cm									
Moment rigidity	Yaw rigidity 0.08 s/N·cm, pitch rigidity 0.06 s/N·cm, roll rigidity 0.06 s/N·cm									
Parallelism	0.030 mm									
Parallelism of motion	0.014 mm									
XY orthogonality	0.010 mm									
Load capacity	95.2 N (9.7 kgf)									
Mass	0.4 kg									
Main materials/surface treatment	Stainless steel/black oxide chrome									




Product Appearance




*TLD-4042-CR1 is a symmetrical type with the same dimensions as TLD-4042-C1.

↑ TLD-4042-C1




*TLD-4042-SR1 is a symmetrical type with the same dimensions as TLD-4042-S1.

↑ TLD-4042-S1




*TLD-4042-CR6 is a symmetrical type with the same dimensions as TLD-4042-C6.

↑ TLD-4042-C6




*TLD-4042-SR6 is a symmetrical type with the same dimensions as TLD-4042-S6.

↑ TLD-4042-S6



*TLD-4042-CR8 is a symmetrical type with the same dimensions as TLD-4042-C8.

↑ TLD-4042-C8




*TLD-4042-SR8 is a symmetrical type with the same dimensions as TLD-4042-S8.

↑ TLD-4042-S8

Motorized Stages	Automated Products for Microscopes	Manual Stages
Fix Stages	Thin VIB Stages	Manual Stages
Rack & Pinion Stages	High-Grade Stages	Stages
Simple Stages, Z Lift Stages, Cross Roller Stages	Tilt/Tilt Stages	Rotary Stages
Z Lift Stages	Stages	Tilt/Rotate Stages
XZ, YZ Stages	Stages	XZ Stages

► Manual Stages ► High-Grade Stages


High-Grade XY Stages 40 x 40 (Stainless Steel)

 HG-VCR method


↑ TLD-4042-S1-2



↑ TLD-4042-S6-2



↑ TLD-4042-S8-2



↑ TLD-4042-SR1-2



↑ TLD-4042-SR6-2



↑ TLD-4042-SR8-2

Features


- A high-accuracy, high-rigidity stage using the HG-VCR method.
- Standard types and symmetrical types are available for a left-right symmetrical structure.
- Feed screws, standard micrometers, and fine pitch micrometers are available for the feed method.
- Clamp method is an operator side plate clamp.
- Versatile use for precision positioning of cameras, sensors, workpieces, and more.

Model number (standard)	TLD-4042-S1-2	TLD-4042-S6-2	TLD-4042-S8-2
Model number (symmetrical)	TLD-4042-SR1-2	TLD-4042-SR6-2	TLD-4042-SR8-2
Model name		High-Grade XY Stage 40 x 40	
Travel direction		XY-axis double direction	
Stage surface		40 mm x 40 mm	
Clamp method		Operator side plate clamp (capable of feeding and clamping the stage on the same surface)	
Operating part mounting position		Side	
Feed method	CMH-13RM (standard micrometer)	Feed screw P=0.5 mm	MHS4-6.5FP (Fine pitch micro)
Travel amount	±6.5 mm		±3 mm
Travel amount/1 knob rotation	0.5 mm		0.1 mm
Scale	Micrometer 0.01 mm	-	Micrometer 0.002 mm
Sensitivity	0.003 mm	0.01 mm	0.001 mm
Travel guide	HG-VCR (V-groove and cross rollers)		
Travel accuracy	Straightness (horizontal/vertical): 0.001 mm Yaw 15 s, pitch 25 s		
Permissible moment	Yaw 500 N·cm, pitch 500 N·cm, roll 500 N·cm		
Moment rigidity	Yaw rigidity 0.08 s/N·cm, pitch rigidity 0.06 s/N·cm, roll rigidity 0.06 s/N·cm		
Parallelism	0.030 mm		
Parallelism of motion	0.014 mm		
XY orthogonality	0.010 mm		
Load capacity	95.2 N (9.7 kgf)		
Mass	0.4 kg		
Main materials/surface treatment	Stainless steel/black oxide chrome		




High-Grade Stages ◇ Manual Stages ◇


Product Appearance



*TLD-4042-SR1-2 is a symmetrical type with the same dimensions as TLD-4042-S1-2. ↑ TLD-4042-S1-2



*TLD-4042-SR6-2 is a symmetrical type with the same dimensions as TLD-4042-S6-2. ↑ TLD-4042-S6-2



*TLD-4042-SR8-2 is a symmetrical type with the same dimensions as TLD-4042-S8-2. ↑ TLD-4042-S8-2

Motorized Stages	Automated Products for Microscopes	Manual Stages
Fix Stages		
Thin VIB Stages		
Rack & Pinion Stages		
High-Grade Stages		
Simp Stages, Z Lift Stages, Cross Roller Stages		
Z Stages		
Rotary Stages		
Tilt/Tilt Stages		
XZ, YZ Stages		
X/Z Stages		

► Manual Stages ► High-Grade Stages


High-Grade XY Stages 50 x 50 (Stainless Steel)

 HG-VCR method


↑ TLD-5042-C1




↑ TLD-5042-C6



↑ TLD-5042-C8



↑ TLD-5042-S1



↑ TLD-5042-S6



↑ TLD-5042-S8


Features

- A high-accuracy, high-rigidity stage using the HG-VCR method.
- Standard types and symmetrical types are available for a left-right symmetrical structure.
- Feed screws, standard micrometers, and fine pitch micrometers are available for the feed method.
- Clamp method is with a plate clamp.
- Versatile use for precision positioning of cameras, sensors, workpieces, and more.

Model number (standard)	TLD-5042-C1	TLD-5042-S1	TLD-5042-C6	TLD-5042-S6	TLD-5042-C8	TLD-5042-S8				
Model number (symmetrical)	TLD-5042-CR1	TLD-5042-SR1	TLD-5042-CR6	TLD-5042-SR6	TLD-5042-CR8	TLD-5042-SR8				
Model name	High-Grade XY Stage 50 x 50									
Travel direction	XY-axis double direction									
Stage surface	50 mm x 50 mm									
Clamp method	Plate clamp									
Operating part mounting position	Center	Side	Center	Side	Center	Side				
Travel mechanism/feed method	CMH-13RM (standard micrometer)		Feed screw P=0.5 mm		MHS4-6.5FP (Fine pitch micro)					
Travel amount	± 6.5 mm			± 3 mm						
Travel amount/1 knob rotation	0.5 mm			0.1 mm						
Scale	Micrometer 0.01 mm		-		Micrometer 0.002 mm					
Sensitivity	0.003 mm		0.01 mm		0.001 mm					
Travel guide	HG-VCR (V-groove and cross rollers)									
Travel accuracy	Straightness (horizontal/vertical): 0.001 mm Yaw 15 s, pitch 25 s									
Permissible moment	Yaw 800 N·cm, pitch 800 N·cm, roll 800 N·cm									
Moment rigidity	Yaw rigidity 0.08 s/N·cm, pitch rigidity 0.06 s/N·cm, roll rigidity 0.06 s/N·cm									
Parallelism	0.030 mm									
Parallelism of motion	0.014 mm									
XY orthogonality	0.010 mm									
Load capacity	144.2 N (14.7 kgf)									
Mass	0.6 kg									
Main materials/surface treatment	Stainless steel/black oxide chrome									




Product Appearance




*TLD-5042-CR1 is a symmetrical type with the same dimensions as TLD-5042-C1.

↑ TLD-5042-C1




*TLD-5042-SR1 is a symmetrical type with the same dimensions as TLD-5042-S1.

↑ TLD-5042-S1




*TLD-5042-CR6 is a symmetrical type with the same dimensions as TLD-5042-C6.

↑ TLD-5042-C6




*TLD-5042-SR6 is a symmetrical type with the same dimensions as TLD-5042-S6.

↑ TLD-5042-S6



*TLD-5042-CR8 is a symmetrical type with the same dimensions as TLD-5042-C8.

↑ TLD-5042-C8



*TLD-5042-SR8 is a symmetrical type with the same dimensions as TLD-5042-S8.

↑ TLD-5042-S8

Motorized Stages	Automated Products for Microscopes	Manual Stages	
Fix Stages			
Thin VIB Stages			
Rack & Pinion Stages			
High-Grade Stages			
Simp Stages, Z Lift Stages, Z Cross Roller Stages			
Rotary Stages			
Tilt/Tilt Stages			
Roll/Rotate Stages			
XZ, YZ Stages			
X/Z Stages			

► Manual Stages ► High-Grade Stages

Motorized Stages

Automated Products for Microscopes

Manual Stages

Fix Stages

Thin VBV Stages

Rack & Pinion Stages

High-Grade Stages

Cross Roller Stages

Z Lift Stages

Rotary Stages

Tilt/Tilt Stages

Tilt/Rotary Stages

XZ, YZ Stages

XYZ Stages

High-Grade XY Stages 50 x 50 (Stainless Steel)

 HG-VCR method

↑ TLD-5042-S1-2



↑ TLD-5042-S6-2



↑ TLD-5042-S8-2



↑ TLD-5042-SR1-2



↑ TLD-5042-SR6-2



↑ TLD-5042-SR8-2


Features

- A high-accuracy, high-rigidity stage using the HG-VCR method.
- Standard types and symmetrical types are available for a left-right symmetrical structure.
- Feed screws, standard micrometers, and fine pitch micrometers are available for the feed method.
- Clamp method is an operator side plate clamp.
- Versatile use for precision positioning of cameras, sensors, workpieces, and more.


Model number (standard)	TLD-5042-S1-2	TLD-5042-S6-2	TLD-5042-S8-2
Model number (symmetrical)	TLD-5042-SR1-2	TLD-5042-SR6-2	TLD-5042-SR8-2
Model name		High-Grade XY Stage 50 x 50	
Travel direction		XY-axis double direction	
Stage surface		50 mm x 50 mm	
Clamp method		Operator side plate clamp (capable of feeding and clamping the stage on the same surface)	
Operating part mounting position		Side	
Feed method	CMH-13RM (standard micrometer)	Feed screw P=0.5 mm	MHS4-6.5FP (Fine pitch micro)
Travel amount	±6.5 mm		±3 mm
Travel amount/1 knob rotation	0.5 mm		0.1 mm
Scale	Micrometer 0.01 mm	-	Micrometer 0.002 mm
Sensitivity	0.003 mm	0.01 mm	0.001 mm
Travel guide	HG-VCR (V-groove and cross rollers)		
Travel accuracy	Straightness (horizontal/vertical): 0.001 mm Yaw 15 s, pitch 25 s		
Permissible moment	Yaw 800 N·cm, pitch 800 N·cm, roll 800 N·cm		
Moment rigidity	Yaw rigidity 0.08 s/N·cm, pitch rigidity 0.06 s/N·cm, roll rigidity 0.06 s/N·cm		
Parallelism	0.030 mm		
Parallelism of motion	0.014 mm		
XY orthogonality	0.010 mm		
Load capacity	144.2 N (14.7 kgf)		
Mass	0.6 kg		
Main materials/surface treatment	Stainless steel/black oxide chrome		




Product Appearance



*TLD-5042-SR1-2 is a symmetrical type with the same dimensions as TLD-5042-S1-2. ↑ TLD-5042-S1-2



*TLD-5042-SR6-2 is a symmetrical type with the same dimensions as TLD-5042-S6-2. ↑ TLD-5042-S6-2



*TLD-5042-SR8-2 is a symmetrical type with the same dimensions as TLD-5042-S8-2. ↑ TLD-5042-S8-2

Motorized Stages	Automated Products for Microscopes	Manual Stages
Fix Stages		
Thin VIB Stages		
Rack & Pinion Stages		
High-Grade Stages		
Sim Stages, Z Lift Stages, Cross Roller Stages		
Z Stages		
Rotary Stages		
Tilt/Tilt Stages		
XZ, YZ Stages		
X/Z Stages		

▶ Manual Stages ▶ High-Grade Stages

High-Grade XY Stages 60 x 60 (Stainless Steel)

 HG-VCR method


↑ TLD-6042-C1



↑ TLD-6042-C6



↑ TLD-6042-C7



↑ TLD-6042-C8



↑ TLD-6042-CR1



↑ TLD-6042-CR6



↑ TLD-6042-CR7



↑ TLD-6042-CR8

Features


- A high-accuracy, high-rigidity stage using the HG-VCR method.
- Standard types and symmetrical types are available for a left-right symmetrical structure.
- Feed screws, standard micrometers, fine pitch micrometers, and digimatic micrometers are available for the feed method.
- Clamp method is with a plate clamp.
- Versatile use for precision positioning of cameras, sensors, workpieces, and more.

Model number (standard)	TLD-6042-C1	TLD-6042-C6	TLD-6042-C7	TLD-6042-C8		
Model number (symmetrical)	TLD-6042-CR1	TLD-6042-CR6	TLD-6042-CR7	TLD-6042-CR8		
Model name	High-Grade XY Stage 60 x 60					
Travel direction	XY-axis double direction					
Stage surface	60 mm x 60 mm					
Clamp method	Plate clamp					
Operating part mounting position	Center					
Feed method	CMH-13RM (Standard micrometer)	Feed screw P=0.5 mm	MHN4-25MX (Digimatic micrometer)	MHS4-6.5FP (Fine pitch micro)		
Travel amount	± 6.5 mm			± 3 mm		
Travel amount/1 knob rotation	0.5 mm			0.1 mm		
Scale	Micrometer 0.01 mm	-	Digital display 0.001 mm	Micrometer 0.002 mm		
Sensitivity	0.003 mm	0.01 mm	0.001 mm			
Travel guide	HG-VCR (V-groove and cross rollers)					
Travel accuracy	Straightness (horizontal/vertical): 0.001 mm Yaw 15 s, pitch 25 s					
Permissible moment	Yaw 1200 N·cm, pitch 1200 N·cm, roll 1200 N·cm					
Moment rigidity	Yaw rigidity 0.08 s/N·cm, pitch rigidity 0.06 s/N·cm, roll rigidity 0.06 s/N·cm					
Parallelism	0.030 mm					
Parallelism of motion	0.014 mm					
XY orthogonality	0.010 mm					
Load capacity	192.1 N (19.6 kgf)					
Mass	0.8 kg	1.2 kg		0.8 kg		
Main materials/surface treatment	Stainless steel/black oxide chrome					




High-Grade Stages ◇ Manual Stages ◇

Product Appearance




*TLD-6042-CR1 is a symmetrical type with the same dimensions as TLD-6042-C1.

↑ TLD-6042-C1




*TLD-6042-CR6 is a symmetrical type with the same dimensions as TLD-6042-C6.

↑ TLD-6042-C6



*TLD-6042-CR7 is a symmetrical type with the same dimensions as TLD-6042-C7.

↑ TLD-6042-C7



*TLD-6042-CR8 is a symmetrical type with the same dimensions as TLD-6042-C8.

↑ TLD-6042-C8

Motorized Stages	Automated Products for Microscopes	Manual Stages
Fix Stages		
Thin VIB Stages		
Rack & Pinion Stages		
High-Grade Stages		
Sim Stages, Z Lift Stages, Cross Roller Stages		
Z Stages		
Rotary Stages		
Tilt/Tilt Stages		
XZ, YZ Stages		
X/Z Stages		

▶ Manual Stages ▶ High-Grade Stages

High-Grade XY Stages 60 x 60 (Stainless Steel)

 HG-VCR method


↑ TLD-6042-S1



↑ TLD-6042-S6



↑ TLD-6042-S7



↑ TLD-6042-S8



↑ TLD-6042-SR1



↑ TLD-6042-SR6



↑ TLD-6042-SR8

Features


- A high-accuracy, high-rigidity stage using the HG-VCR method.
- Standard types and symmetrical types are available for a left-right symmetrical structure.
- Feed screws, standard micrometers, fine pitch micrometers, and digimatic micrometers are available for the feed method.
- Clamp method is with a plate clamp.
- Versatile use for precision positioning of cameras, sensors, workpieces, and more.

Model number (standard)	TLD-6042-S1	TLD-6042-S6	TLD-6042-S7	TLD-6042-S8
Model number (symmetrical)	TLD-6042-SR1	TLD-6042-SR6	-	TLD-6042-SR8
Model name		High-Grade XY Stage 60 x 60		
Travel direction		XY-axis double direction		
Stage surface		60 mm x 60 mm		
Clamp method		Plate clamp		
Operating part mounting position		Side		
Feed method	CMH-13RM (Standard micrometer)	Feed screw P=0.5 mm	MHN4-25MX (Digimatic micrometer)	MHS4-6.5FP (Fine pitch micro)
Travel amount		±6.5 mm		±3 mm
Travel amount/1 knob rotation		0.5 mm		0.1 mm
Scale	Micrometer 0.01 mm	-	Digital display 0.001 mm	Micrometer 0.002 mm
Sensitivity	0.003 mm	0.01 mm		0.001 mm
Travel guide	HG-VCR (V-groove and cross rollers)			
Travel accuracy	Straightness (horizontal/vertical): 0.001 mm Yaw 15 s, pitch 25 s			
Permissible moment	Yaw 1200 N·cm, pitch 1200 N·cm, roll 1200 N·cm			
Moment rigidity	Yaw rigidity 0.08 s/N·cm, pitch rigidity 0.06 s/N·cm, roll rigidity 0.06 s/N·cm			
Parallelism	0.030 mm			
Parallelism of motion	0.014 mm			
XY orthogonality	0.010 mm			
Load capacity	192.1 N (19.6 kgf)			
Mass	0.8 kg		1.2 kg	0.8 kg
Main materials/surface treatment	Stainless steel/black oxide chrome			




High-Grade Stages ◇ Manual Stages ◇

Product Appearance




*TLD-6042-SR1 is a symmetrical type with the same dimensions as TLD-6042-S1.

↑ TLD-6042-S1




*TLD-6042-SR6 is a symmetrical type with the same dimensions as TLD-6042-S6.

↑ TLD-6042-S6



↑ TLD-6042-S7



*TLD-6042-SR8 is a symmetrical type with the same dimensions as TLD-6042-S8.

↑ TLD-6042-S8

Motorized Stages	Automated Products for Microscopes	Manual Stages
Fix Stages		
Thin VIB Stages		
Rack & Pinion Stages		
High-Grade Stages		
Simp Stages, Z Lift Stages, Cross Roller Stages		
Z Stages		
Rotary Stages		
Tilt/Tilt Stages		
XZ, YZ Stages		
X/Z Stages		

▶ Manual Stages ▶ High-Grade Stages


High-Grade XY Stages 60 x 60 (Stainless Steel)

 HG-VCR method


↑ TLD-6042-S1-2



↑ TLD-6042-S6-2



↑ TLD-6042-S7-2



↑ TLD-6042-S8-2



↑ TLD-6042-SR1-2



↑ TLD-6042-SR6-2



↑ TLD-6042-SR8-2

Features


- A high-accuracy, high-rigidity stage using the HG-VCR method.
- Standard types and symmetrical types are available for a left-right symmetrical structure.
- Feed screws, standard micrometers, fine pitch micrometers, and digimatic micrometers are available for the feed method.
- Clamp method is an operator side plate clamp.
- Versatile use for precision positioning of cameras, sensors, workpieces, and more.

Model number (standard)	TLD-6042-S1-2	TLD-6042-S6-2	TLD-6042-S7-2	TLD-6042-S8-2		
Model number (symmetrical)	TLD-6042-SR1-2	TLD-6042-SR6-2	-	TLD-6042-SR8-2		
Model name	High-Grade XY Stage 60 x 60					
Travel direction	XY-axis double direction					
Stage surface	60 mm x 60 mm					
Clamp method	Operator side plate clamp (capable of feeding and clamping the stage on the same surface)					
Operating part mounting position	Side					
Feed method	CMH-13RM (Standard micrometer)	Feed screw P=0.5 mm	MHN4-25MX (Digimatic micrometer)	MHS4-6.5FP (Fine pitch micro)		
Travel amount	± 6.5 mm			± 3 mm		
Travel amount/1 knob rotation	0.5 mm			0.1 mm		
Scale	Micrometer 0.01 mm	-	Digital display 0.001 mm	Micrometer 0.002 mm		
Sensitivity	0.003 mm	0.01 mm	0.001 mm			
Travel guide	HG-VCR (V-groove and cross rollers)					
Travel accuracy	Straightness (horizontal/vertical): 0.001 mm Yaw 15 s, pitch 25 s					
Permissible moment	Yaw 1200 N·cm, pitch 1200 N·cm, roll 1200 N·cm					
Moment rigidity	Yaw rigidity 0.08 s/N·cm, pitch rigidity 0.06 s/N·cm, roll rigidity 0.06 s/N·cm					
Parallelism	0.030 mm					
Parallelism of motion	0.014 mm					
XY orthogonality	0.010 mm					
Load capacity	192.1 N (19.6 kgf)					
Mass	0.8 kg	1.2 kg		0.8 kg		
Main materials/surface treatment	Stainless steel/black oxide chrome					


High-Grade Stages ◇ Manual Stages ◇




Product Appearance




*TLD-6042-SR1-2 is a symmetrical type with the same dimensions as TLD-6042-S1-2. ↑ TLD-6042-S1-2



*TLD-6042-SR6-2 is a symmetrical type with the same dimensions as TLD-6042-S6-2. ↑ TLD-6042-S6-2



↑ TLD-6042-S7-2



*TLD-6042-SR8-2 is a symmetrical type with the same dimensions as TLD-6042-S8-2. ↑ TLD-6042-S8-2

MotORIZED
Stages

Automated
Products for
Microscopes

Manual Stages

Fix Stages

Thin VIB
Stages

Rack & Pinion
Stages

High-Grade
Stages

Slim Stages,
Z Lift Stages,
Cross Roller
Stages

Z Stages

Rotary Stages

Tilt/Tilt Stages

XZ, YZ Stages

Tilt/Rotate
Stages

X/Z Stages

► Manual Stages ► High-Grade Stages

High-Grade XY Stages 70 x 70 (Stainless Steel)

 HG-VCR method


↑ TLD-7042-C1



↑ TLD-7042-C6



↑ TLD-7042-C7




↑ TLD-7042-C8



↑ TLD-7042-CR1



↑ TLD-7042-CR6



↑ TLD-7042-CR7



↑ TLD-7042-CR8

Features


- A high-accuracy, high-rigidity stage using the HG-VCR method.
- Standard types and symmetrical types are available for a left-right symmetrical structure.
- Feed screws, standard micrometers, fine pitch micrometers, and digimatic micrometers are available for the feed method.
- Clamp method is with a plate clamp.
- Versatile use for precision positioning of cameras, sensors, workpieces, and more.

Model number (standard)	TLD-7042-C1	TLD-7042-C6	TLD-7042-C7	TLD-7042-C8		
Model number (symmetrical)	TLD-7042-CR1	TLD-7042-CR6	TLD-7042-CR7	TLD-7042-CR8		
Model name	High-Grade XY Stage 70 x 70					
Travel direction	XY-axis double direction					
Stage surface	70 mm x 70 mm					
Clamp method	Plate clamp					
Operating part mounting position	Center					
Feed method	CMH-13RM (Standard micrometer)	Feed screw P=0.5 mm	MHN4-25MX (Digimatic micrometer)	MHS4-6.5FP (Fine pitch micro)		
Travel amount	± 6.5 mm			± 3 mm		
Travel amount/1 knob rotation	0.5 mm			0.1 mm		
Scale	Micrometer 0.01 mm	-	Digital display 0.001 mm	Micrometer 0.002 mm		
Sensitivity	0.003 mm	0.01 mm	0.001 mm			
Travel guide	HG-VCR (V-groove and cross rollers)					
Travel accuracy	Straightness (horizontal/vertical): 0.001 mm Yaw 15 s, pitch 25 s					
Permissible moment	Yaw 1500 N·cm, pitch 1500 N·cm, roll 1500 N·cm					
Moment rigidity	Yaw rigidity 0.08 s/N·cm, pitch rigidity 0.06 s/N·cm, roll rigidity 0.06 s/N·cm					
Parallelism	0.030 mm					
Parallelism of motion	0.014 mm					
XY orthogonality	0.010 mm					
Load capacity	239.1 N (24.4 kgf)					
Mass	1.2 kg	1.6 kg		1.2 kg		
Main materials/surface treatment	Stainless steel/black oxide chrome					

High-Grade Stages ◇ Manual Stages ◇




Product Appearance




*TLD-7042-CR1 is a symmetrical type with the same dimensions as TLD-7042-C1.

↑ TLD-7042-C1




*TLD-7042-CR6 is a symmetrical type with the same dimensions as TLD-7042-C6.

↑ TLD-7042-C6



*TLD-7042-CR7 is a symmetrical type with the same dimensions as TLD-7042-C7.

↑ TLD-7042-C7



*TLD-7042-CR8 is a symmetrical type with the same dimensions as TLD-7042-C8.

↑ TLD-7042-C8

Motorized
StagesAutomated
Products for
Microscopes

Fix Stages

Thin VIB
StagesRack & Pinion
StagesHigh-Grade
StagesSimple Stages,
Z Lift Stages,
Cross Roller
Stages

Z Lift Stages

Rotary Stages

Tilt/Rotate
Stages

XZ, YZ Stages

XZ Stages

► Manual Stages ► High-Grade Stages

Motorized
StagesAutomated
Products for
Microscopes

Manual Stages

Fix Stages

Thin VBV
StagesRack & Pinion
StagesHigh-Grade
StagesSeri Stages,
Cross Roller
Stages

Z Lift Stages,

Tilt/Til Stages

Rotary Stages

Tilt/Rotary
Stages

XZ, YZ Stages

XYZ Stages

High-Grade XY Stages 70 x 70 (Stainless Steel)

 HG-VCR
method

↑ TLD-7042-S1



↑ TLD-7042-S6



↑ TLD-7042-S7



↑ TLD-7042-S8



↑ TLD-7042-SR1



↑ TLD-7042-SR6



↑ TLD-7042-SR8

Features


- A high-accuracy, high-rigidity stage using the HG-VCR method.
- Standard types and symmetrical types are available for a left-right symmetrical structure.
- Feed screws, standard micrometers, fine pitch micrometers, and digimatic micrometers are available for the feed method.
- Clamp method is with a plate clamp.
- Versatile use for precision positioning of cameras, sensors, workpieces, and more.

Model number (standard)	TLD-7042-S1	TLD-7042-S6	TLD-7042-S7	TLD-7042-S8
Model number (symmetrical)	TLD-7042-SR1	TLD-7042-SR6	-	TLD-7042-SR8
Model name		High-Grade XY Stage 70 x 70		
Travel direction		XY-axis double direction		
Stage surface		70 mm x 70 mm		
Clamp method		Plate clamp		
Operating part mounting position		Side		
Feed method	CMH-13RM (Standard micrometer)	Feed screw P=0.5 mm	MHN4-25MX (Digimatic micrometer)	MHS4-6.5FP (Fine pitch micro)
Travel amount		±6.5 mm		±3 mm
Travel amount/1 knob rotation		0.5 mm		0.1 mm
Scale	Micrometer 0.01 mm	-	Digital display 0.001 mm	Micrometer 0.002 mm
Sensitivity	0.003 mm	0.01 mm		0.001 mm
Travel guide		HG-VCR (V-groove and cross rollers)		
Travel accuracy		Straightness (horizontal/vertical): 0.001 mm Yaw 15 s, pitch 25 s		
Permissible moment		Yaw 1500 N·cm, pitch 1500 N·cm, roll 1500 N·cm		
Moment rigidity		Yaw rigidity 0.08 s/N·cm, pitch rigidity 0.06 s/N·cm, roll rigidity 0.06 s/N·cm		
Parallelism		0.030 mm		
Parallelism of motion		0.014 mm		
XY orthogonality		0.010 mm		
Load capacity		239.1 N (24.4 kgf)		
Mass	1.2 kg		1.6 kg	1.2 kg
Main materials/surface treatment		Stainless steel/black oxide chrome		

High-Grade Stages ◀ Manual Stages ◀




Product Appearance




*TLD-7042-SR1 is a symmetrical type with the same dimensions as TLD-7042-S1.

↑ TLD-7042-S1




*TLD-7042-SR6 is a symmetrical type with the same dimensions as TLD-7042-S6.

↑ TLD-7042-S6



↑ TLD-7042-S7



*TLD-7042-SR8 is a symmetrical type with the same dimensions as TLD-7042-S8.

↑ TLD-7042-S8

Motorized Stages	Automated Products for Microscopes	Manual Stages
Fix Stages		
Thin VIB Stages		
Rack & Pinion Stages		
High-Grade Stages		
Simp Stages, Z Lift Stages, Cross Router Stages		
Z Stages		
Rotary Stages		
Tilt/Tilt Stages		
XZ, YZ Stages		
XZ Stages		

▶ Manual Stages ▶ High-Grade Stages

High-Grade XY Stages 70 x 70 (Stainless Steel)

 HG-VCR method


↑ TLD-7042-S1-2



↑ TLD-7042-S6-2



↑ TLD-7042-S7-2



↑ TLD-7042-S8-2



↑ TLD-7042-SR1-2



↑ TLD-7042-SR6-2



↑ TLD-7042-SR8-2

Features


- A high-accuracy, high-rigidity stage using the HG-VCR method.
- Standard types and symmetrical types are available for a left-right symmetrical structure.
- Feed screws, standard micrometers, fine pitch micrometers, and digimatic micrometers are available for the feed method.
- Clamp method is an operator side plate clamp.
- Versatile use for precision positioning of cameras, sensors, workpieces, and more.

Model number (standard)	TLD-7042-S1-2	TLD-7042-S6-2	TLD-7042-S7-2	TLD-7042-S8-2		
Model number (symmetrical)	TLD-7042-SR1-2	TLD-7042-SR6-2	-	TLD-7042-SR8-2		
Model name	High-Grade XY Stage 70 x 70					
Travel direction	XY-axis double direction					
Stage surface	70 mm x 70 mm					
Clamp method	Operator side plate clamp (capable of feeding and clamping the stage on the same surface)					
Operating part mounting position	Side					
Feed method	CMH-13RM (Standard micrometer)	Feed screw P=0.5 mm	MHN4-25MX (Digimatic micrometer)	MHS4-6.5FP (Fine pitch micro)		
Travel amount	± 6.5 mm			± 3 mm		
Travel amount/1 knob rotation	0.5 mm			0.1 mm		
Scale	Micrometer 0.01 mm	-	Digital display 0.001 mm	Micrometer 0.002 mm		
Sensitivity	0.003 mm	0.01 mm	0.001 mm			
Travel guide	HG-VCR (V-groove and cross rollers)					
Travel accuracy	Straightness (horizontal/vertical): 0.001 mm Yaw 15 s, pitch 25 s					
Permissible moment	Yaw 1500 N·cm, pitch 1500 N·cm, roll 1500 N·cm					
Moment rigidity	Yaw rigidity 0.08 s/N·cm, pitch rigidity 0.06 s/N·cm, roll rigidity 0.06 s/N·cm					
Parallelism	0.030 mm					
Parallelism of motion	0.014 mm					
XY orthogonality	0.010 mm					
Load capacity	239.1 N (24.4 kgf)					
Mass	1.2 kg	1.6 kg		1.2 kg		
Main materials/surface treatment	Stainless steel/black oxide chrome					




High-Grade Stages ◀ Manual Stages ◀


Product Appearance




*TLD-7042-SR1-2 is a symmetrical type with the same dimensions as TLD-7042-S1-2.



*TLD-7042-SR6-2 is a symmetrical type with the same dimensions as TLD-7042-S6-2. [↑ TLD-7042-S6-2](#)



↑ TLD-7042-S7-2



*TLD-7042-SR8-2 is a symmetrical type with the same dimensions as TLD-7042-S8-2.

Motorized Stages	Automated Products for Microscopes	Manual Stages
Fix Stages	Thin VB Stages	Rock & Phon Stages
	Stages	Stages
	High-Grade Cross Roller Stages	Stages
	Stages	Z Stages
	Stages	Rotary Stages
	Stages	Tilt Stages
	Stages	TR/Tilt Stages
	Stages	XZ/YZ Stages
	Stages	XYZ Stages